

Quick Star Push-in Connectors – Inch Series



QSM – Mini Series:
Tubing O.D. from 1/8" to 3/16"

QS – Standard Series:
Tubing O.D. from 1/8" to 5/8"

For complete dimensional and technical information, visit: www.festo.com/us and view our online catalog, or contact your Product Support team via:
Phone: 1.800.99.FESTO (1.800.993.3786)
Email: product.support@us.festo.com

Quick Star Push-in Connectors – Inch Series

FESTO

Push-in Straight Connector



| Ordering Data | | |
|---------------|-------------|---------------------------------|
| Part No. | Type | For Tubing O.D. D1 [inch] |
| 153905* | QSM-1/8T-U | 1/8 |
| 195588* | QSM-5/32T-U | 5/32 |
| 153628* | QS-5/32T-U | 5/32 |
| 153629* | QS-3/16T-U | 3/16 |
| 153630* | QS-1/4T-U | 1/4 |
| 153631* | QS-5/16T-U | 5/16 |
| 153632* | QS-3/8T-U | 3/8 |
| 153633 | QS-1/2T-U | 1/2 |
| 190589* | QS-5/8T-U | 5/8 |

2

2.1

Push-in Reducing Straight Connector



| Ordering Data | | | |
|---------------|-----------------|---------------------------------|---------------------------------|
| Part No. | Type | For Tubing O.D. D1 [inch] | For Tubing O.D. D2 [inch] |
| 153906* | QSM-5/32T-1/8-U | 5/32 | 1/8 |
| 153634* | QS-3/16T-5/32-U | 3/16 | 5/32 |
| 190590* | QS-1/4T-5/32-U | 1/4 | 5/32 |
| 153635* | QS-1/4T-3/16-U | 1/4 | 3/16 |
| 153636* | QS-5/16T-1/4-U | 5/16 | 1/4 |
| 153637* | QS-3/8T-5/16-U | 3/8 | 5/16 |
| 153638 | QS-1/2T-3/8-U | 1/2 | 3/8 |
| 190591* | QS-5/8T-1/2-U | 5/8 | 1/2 |

Push-in Straight Connector, with Internal Shut-off



| Ordering Data | | |
|---------------|--------------|---------------------------------|
| Part No. | Type | For Tubing O.D. D1 [inch] |
| 190592 | QSMK-1/8T-U | 1/8 |
| 190593 | QSMK-5/32T-U | 5/32 |
| 190594 | QSMK-3/16T-U | 3/16 |
| 190595 | QSK-1/4T-U | 1/4 |
| 190596 | QSK-5/16T-U | 5/16 |
| 190597 | QSK-3/8T-U | 3/8 |
| 190598 | QSK-1/2T-U | 1/2 |

* Packaged in quantities of 10. (No asterisk = items sold by the unit.)
Ask Festo or your authorized Festo distributor about part numbers of items offered in bulk package sizes.

Quick Star Push-in Connectors – Inch Series

Push-in Reducing Straight Connector with Insert



| Ordering Data | | | |
|---------------|------------------|---------------------------|---------------------------|
| Part No. | Type | For Tubing O.D. D1 [inch] | For Tubing O.D. D2 [inch] |
| 190613* | QSM-5/32H-1/8-U | 5/32 | 1/8 |
| 190614* | QSM-3/16H-5/32-U | 3/16 | 5/32 |
| 190615* | QS-1/4H-3/16-U | 1/4 | 3/16 |
| 190616* | QS-5/16H-1/4-U | 5/16 | 1/4 |
| 190617* | QS-3/8H-5/16-U | 3/8 | 5/16 |
| 190618* | QS-1/2H-3/8-U | 1/2 | 3/8 |

Push-in Elbow Connector



| Ordering Data | | |
|---------------|--------------|---------------------------|
| Part No. | Type | For Tubing O.D. D1 [inch] |
| 153913* | QSML-1/8T-U | 1/8 |
| 190602* | QSML-5/32T-U | 5/32 |
| 153662* | QSL-5/32T-U | 5/32 |
| 153663* | QSL-3/16T-U | 3/16 |
| 153664* | QSL-1/4T-U | 1/4 |
| 153665* | QSL-5/16T-U | 5/16 |
| 153666* | QSL-3/8T-U | 3/8 |
| 153667 | QSL-1/2T-U | 1/2 |
| 190603* | QSL-5/8T-U | 5/8 |

Push-in Elbow Connector, with Insert



| Ordering Data | | |
|---------------|--------------|---------------------------|
| Part No. | Type | For Tubing O.D. D1 [inch] |
| 190620* | QSML-1/8H-U | 1/8 |
| 190621* | QSML-5/32H-U | 5/32 |
| 190622* | QSML-3/16H-U | 3/16 |
| 153654* | QSL-1/4H-U | 1/4 |
| 153655* | QSL-5/16H-U | 5/16 |
| 153656* | QSL-3/8H-U | 3/8 |
| 190623* | QSL-1/2H-U | 1/2 |

* Packaged in quantities of 10. (No asterisk = items sold by the unit.)
Ask Festo or your authorized Festo distributor about part numbers of items offered in bulk package sizes.

Quick Star Push-in Connectors – Inch Series

Push-in Elbow Connector, with Long Insert



| Ordering Data | | |
|---------------|---------------|---------------------------|
| Part No. | Type | For Tubing O.D. D1 [inch] |
| 190636* | QSML-3/16HL-U | 3/16 |
| 190635* | QSL-5/32HL-U | 5/32 |
| 153659* | QSL-1/4HL-U | 1/4 |
| 153660* | QSL-5/16HL-U | 5/16 |
| 153661* | QSL-3/8HL-U | 3/8 |
| 190637* | QSL-1/2HL-U | 1/2 |

Push-in Reducing Elbow Connector, with Insert



| Ordering Data | | | |
|---------------|-------------------|---------------------------|---------------------------|
| Part No. | Type | For Tubing O.D. D1 [inch] | For Tubing O.D. D2 [inch] |
| 190625* | QSML-5/32H-1/8-U | 5/32 | 1/8 |
| 190626* | QSML-3/16H-1/8-U | 3/16 | 1/8 |
| 190627* | QSML-3/16H-5/32-U | 3/16 | 5/32 |
| 190628* | QSL-1/4H-5/32-U | 1/4 | 5/32 |
| 190629* | QSL-1/4H-3/16-U | 1/4 | 3/16 |
| 190630* | QSL-5/16H-3/16-U | 5/16 | 3/16 |
| 153657* | QSL-5/16H-1/4-U | 5/16 | 1/4 |
| 190631* | QSL-3/8H-1/4-U | 3/8 | 1/4 |
| 153658* | QSL-3/8H-5/16-U | 3/8 | 5/16 |
| 190632* | QSL-1/2H-5/16-U | 1/2 | 5/16 |
| 190633* | QSL-1/2H-3/8-U | 1/2 | 3/8 |

Push-in Y Connector



| Ordering Data | | |
|---------------|--------------|---------------------------|
| Part No. | Type | For Tubing O.D. D1 [inch] |
| 153921* | QSMY-1/8T-U | 1/8 |
| 190608* | QSMY-5/32T-U | 5/32 |
| 153750* | QSY-5/32T-U | 5/32 |
| 153751* | QSY-3/16T-U | 3/16 |
| 153752* | QSY-1/4T-U | 1/4 |
| 153753* | QSY-5/16T-U | 5/16 |
| 153754* | QSY-3/8T-U | 3/8 |
| 153755 | QSY-1/2T-U | 1/2 |

* Packaged in quantities of 10. (No asterisk = items sold by the unit.)
Ask Festo or your authorized Festo distributor about part numbers of items offered in bulk package sizes.

Quick Star Push-in Connectors – Inch Series

Push-in Reducing Y Connector



| Ordering Data | | | |
|---------------|------------------|---------------------------|---------------------------|
| Part No. | Type | For Tubing O.D. D1 [inch] | For Tubing O.D. D2 [inch] |
| 153922* | QSMY-5/32T-1/8-U | 5/32 | 1/8 |
| 153756* | QSY-3/16T-5/32-U | 3/16 | 5/32 |
| 153757* | QSY-1/4T-3/16-U | 1/4 | 3/16 |
| 153758* | QSY-5/16T-1/4-U | 5/16 | 1/4 |
| 153759* | QSY-3/8T-5/16-U | 3/8 | 5/16 |
| 153760 | QSY-1/2T-3/8-U | 1/2 | 3/8 |

Push-in Reducing Double Y Connector



| Ordering Data | | | |
|---------------|------------------|---------------------------|---------------------------|
| Part No. | Type | For Tubing O.D. D1 [inch] | For Tubing O.D. D2 [inch] |
| 153814* | QSQ-3/16T-5/32-U | 3/16 | 5/32 |
| 153815* | QSQ-1/4T-5/32-U | 1/4 | 5/32 |
| 190609* | QSQ-1/4T-3/16-U | 1/4 | 3/16 |
| 153816 | QSQ-5/16T-1/4-U | 5/16 | 1/4 |

Push-in T Connector



| Ordering Data | | |
|---------------|--------------|---------------------------|
| Part No. | Type | For Tubing O.D. D1 [inch] |
| 153920* | QSMT-1/8T-U | 1/8 |
| 190604* | QSMT-5/32T-U | 5/32 |
| 153724* | QST-5/32T-U | 5/32 |
| 153725* | QST-3/16T-U | 3/16 |
| 153726* | QST-1/4T-U | 1/4 |
| 153727* | QST-5/16T-U | 5/16 |
| 153728* | QST-3/8T-U | 3/8 |
| 153729 | QST-1/2T-U | 1/2 |
| 190606* | QST-5/8T-U | 5/8 |

* Packaged in quantities of 10. (No asterisk = items sold by the unit.)
 Ask Festo or your authorized Festo distributor about part numbers of items offered in bulk package sizes.

Push-in Reducing T Connector



| Ordering Data | | | |
|---------------|------------------|---------------------------|---------------------------|
| Part No. | Type | For Tubing O.D. D1 [inch] | For Tubing O.D. D2 [inch] |
| 190605* | QSMT-5/32T-1/8-U | 5/32 | 1/8 |
| 153730* | QST-3/16T-5/32-U | 3/16 | 5/32 |
| 153731* | QST-1/4T-3/16-U | 1/4 | 3/16 |
| 153732* | QST-5/16T-1/4-U | 5/16 | 1/4 |
| 153733* | QST-3/8T-5/16-U | 3/8 | 5/16 |
| 153734 | QST-1/2T-3/8-U | 1/2 | 3/8 |
| 190607* | QST-5/8T-1/2-U | 5/8 | 1/2 |

Push-in Triple Branch Reducing T Connector



| Ordering Data | | | |
|---------------|-------------------|---------------------------|---------------------------|
| Part No. | Type | For Tubing O.D. D1 [inch] | For Tubing O.D. D2 [inch] |
| 153804 | QST3-3/16T-5/32-U | 3/16 | 5/32 |
| 153805 | QST3-5/16T-5/32-U | 5/16 | 5/32 |
| 153806 | QST3-5/16T-3/16-U | 5/16 | 3/16 |
| 153807 | QST3-5/16T-1/4-U | 5/16 | 1/4 |
| 153808 | QST3-3/8T-1/4-U | 3/8 | 1/4 |
| 153809 | QST3-3/8T-5/16-U | 3/8 | 5/16 |

Push-in X Connector



| Ordering Data | | |
|---------------|--------------|---------------------------|
| Part No. | Type | For Tubing O.D. D1 [inch] |
| 153923* | QSMX-1/8T-U | 1/8 |
| 190610* | QSMX-5/32T-U | 5/32 |
| 190611* | QSX-3/16T-U | 3/16 |
| 190612* | QSX-1/4T-U | 1/4 |
| 153840* | QSX-5/16T-U | 5/16 |
| 153841* | QSX-3/8T-U | 3/8 |
| 153842* | QSX-1/2T-U | 1/2 |

* Packaged in quantities of 10. (No asterisk = items sold by the unit.)
 Ask Festo or your authorized Festo distributor about part numbers of items offered in bulk package sizes.

Push-in Bulkhead Connector



| Ordering Data | | |
|---------------|--------------|---------------------------------|
| Part No. | Type | For Tubing O.D. D1 [inch] |
| 190599* | QSMS-1/8T-U | 1/8 |
| 190600* | QSMS-5/32T-U | 5/32 |
| 153761* | QSS-5/32T-U | 5/32 |
| 153762* | QSS-3/16T-U | 3/16 |
| 153763* | QSS-1/4T-U | 1/4 |
| 153764* | QSS-5/16T-U | 5/16 |
| 153765* | QSS-3/8T-U | 3/8 |
| 153766* | QSS-1/2T-U | 1/2 |
| 190601* | QSS-5/8T-U | 5/8 |

Push-in Cap



| Ordering Data | | |
|---------------|------------|---------------------------------|
| Part No. | Type | For Tubing O.D. D1 [inch] |
| 153925* | QSC-1/8-U | 1/8 |
| 153828* | QSC-5/32-U | 5/32 |
| 153829* | QSC-3/16-U | 3/16 |
| 153830* | QSC-1/4-U | 1/4 |
| 153831* | QSC-5/16-U | 5/16 |
| 153832* | QSC-3/8-U | 3/8 |
| 153833* | QSC-1/2-U | 1/2 |

Blanking Plug



| Ordering Data | | |
|---------------|-------------|-------------------------------|
| Part No. | Type | Plug Diameter D1 [inch] |
| 153924* | QSMC-1/8H-U | 1/8 |
| 153834* | QSC-5/32H-U | 5/32 |
| 153835* | QSC-3/16H-U | 3/16 |
| 153836* | QSC-1/4H-U | 1/4 |
| 153837* | QSC-5/16H-U | 5/16 |
| 153838* | QSC-3/8H-U | 3/8 |
| 153839 | QSC-1/2H-U | 1/2 |
| 190640* | QSC-5/8H-U | 5/8 |

* Packaged in quantities of 10. (No asterisk = items sold by the unit.)
Ask Festo or your authorized Festo distributor about part numbers of items offered in bulk package sizes.

Push-in Insert



| Ordering Data | | |
|---------------|------------|---------------------------|
| Part No. | Type | Insert Diameter D1 [inch] |
| 153817* | QSH-5/32-U | 5/32 |
| 153818* | QSH-3/16-U | 3/16 |
| 153819* | QSH-1/4-U | 1/4 |
| 153820* | QSH-5/16-U | 5/16 |
| 153821* | QSH-3/8-U | 3/8 |
| 153822 | QSH-1/2-U | 1/2 |
| 190641* | QSH-5/8-U | 5/8 |

2

Push-in Reducing Insert



| Ordering Data | | | |
|---------------|-----------------|---------------------------|---------------------------|
| Part No. | Type | Insert Diameter D1 [inch] | Insert Diameter D2 [inch] |
| 153823* | QSH-3/16-5/32-U | 3/16 | 5/32 |
| 153824* | QSH-1/4-3/16-U | 1/4 | 3/16 |
| 153825* | QSH-5/16-1/4-U | 5/16 | 1/4 |
| 153826* | QSH-3/8-5/16-U | 3/8 | 5/16 |
| 153827* | QSH-1/2-3/8-U | 1/2 | 3/8 |
| 190642* | QSH-5/8-1/2-U | 5/8 | 1/2 |

* Packaged in quantities of 10. (No asterisk = items sold by the unit.)
 Ask Festo or your authorized Festo distributor about part numbers of items offered in bulk package sizes.

2.1

Festo - Your Partner in Automation



1 Festo Inc.
5300 Explorer Drive
Mississauga, ON L4W 5G4
Canada

Festo Customer Interaction Center
Tel: 1 877 463 3786
Fax: 1 877 393 3786
Email: customer.service.ca@festo.com

2 Festo Pneumatic
Av. Ceylán 3,
Col. Tequesquináhuac
54020 Tlalneantla,
Estado de México

Multinational Contact Center
01 800 337 8669
ventas.mexico@festo.com

3 Festo Corporation
1377 Motor Parkway
Suite 310
Islandia, NY 11749

Festo Customer Interaction Center
1 800 993 3786
1 800 963 3786
customer.service.us@festo.com

4 Regional Service Center
7777 Columbia Road
Mason, OH 45040

Connect with us



www.festo.com/socialmedia



www.festo.com

Subject to change