

Adapter plate kit EHAM




Key features and datasheet

At a glance

The adapter plate kits are used for mounting the dispense heads and dispense heads/valve control module VTOF, VTOE, VTOI and VAEM on the electric slides EGSC and EGSK.

Example: Combination of EGSC and VTOI




Dispense heads/valve control module	Electric slides			
	EGSK-20	EGSK-26	EGSC-25	EGSC-32
VTOF1-...	EHAM-MA-E19-25-C11	-	-	-
VTOF4-...	-	EHAM-MA-E19-25-C11	-	-
VTOF8-...	-	-	EHAM-MA-E19-25-C11	-
VTOF12-...	-	-	-	EHAM-MA-E19-25-C11
VTOE-...	-	-	-	EHAM-MA-E19-25-C11
VTOI-...	EHAM-MA-E19-25-C14			
VAEM-V-S8EPRS2	EHAM-MA-E19-25-V3			

Technical data				
Type		EHAM-MA-E19-25-C11	EHAM-MA-E19-25-C14	EHAM-MA-E19-25-V3
Design		Mounting kit		
Type of mounting		With through-hole and screw		
Mounting position		Vertical		
Ambient temperature	[°C]	-20 ... +80		
Corrosion resistance class CRC ²⁾		2		
Product weight	[g]	71	72.3	135
Adapter plate material		Anodised aluminium		
Screws material		Steel		
Centring elements material		High-alloy steel		
Note on materials		RoHS-compliant		

Datasheet

Dimensions – EHAM-MA-E19-25-C11


Download CAD data → www.festo.com



Type	B1	H1	H2	H3	L1	L2	L3	L4
EHAM-MA-E19-25-C11	7	90	10	15	64	55	19	36

Dimensions – EHAM-MA-E19-25-C14

Download CAD data → www.festo.com




- [1] Socket head screw ISO 4762 M3x5-8.8
- [2] Socket head screw ISO 4762 M3x14-A2-70
- [3] Socket head screw ISO 4032 M3-A2-70
- [4] Socket head screw ISO 4762 M3x8-8.8
- [5] Socket head screw ISO 4762 M4x8-8.8
- [6] Centring pin ZBS-5
- [7] Centring pin ZBS-4
- [8] Centring pin ZBS-2

Type	B1	B2	B3	B4	H1	H2	H3	L1	W1
EHAM-MA-E19-25-C14	7	58.5	53	15.5	78	24	15.5	36	15°

Datasheet

Dimensions – EHAM-MA-E19-25-V3

Download CAD data → www.festo.com



Type	B1	H1	H2	H3	H4	H5	L1	L2	L3
EHAM-MA-E19-25-V3	7	74	50	10	8	6	94	83	36

Ordering data

	Description	Part no.	Type
EHAM-MA-E19-25-C11	For VTOF and VTOE	8140774	EHAM-MA-E19-25-C11
EHAM-MA-E19-25-C14	For VTOI	8140775	EHAM-MA-E19-25-C14
EHAM-MA-E19-25-V3	For VAEM-VS8EPRS2	8140776	EHAM-MA-E19-25-V3

Festo - Your Partner in Automation



1 Festo Inc.
5300 Explorer Drive
Mississauga, ON L4W 5G4
Canada

Festo Customer Interaction Center
Tel: 1 877 463 3786
Fax: 1 877 393 3786
Email: customer.service.ca@festo.com



2 Festo Pneumatic
Av. Ceylán 3,
Col. Tequesquináhuac
54020 Tlalnepantla,
Estado de México

Multinational Contact Center
01 800 337 8669
ventas.mexico@festo.com



3 Festo Corporation
1377 Motor Parkway
Suite 310
Islandia, NY 11749

Festo Customer Interaction Center
1 800 993 3786
1 800 963 3786
customer.service.us@festo.com



4 Regional Service Center
7777 Columbia Road
Mason, OH 45040

Connect with us



www.festo.com/socialmedia



www.festo.com

Subject to change