

Accessories for valves and valve terminals VAME, mounting attachments

FESTO


Technical data

Mounting attachments enable valve terminals to be attached to walls and machine parts.





Examples illustrating H-rail mounting

Via mounting rail



The valve terminal is attached to the H-rail (see arrow A) and then swivelled onto the H-rail and secured in place with the clamping component (see arrow B).

- 1 Holes for wall mounting
- 2 Self-tapping M4x10 screw of the H-rail clamping unit
- 3 Clamping component of the H-rail clamping unit

Ordering data						
	Weight [g]	Material	Function	Dimensions [mm]	Part No.	Type
	35.1	Steel/polymer	Base for H-rail mounting. Is screwed onto the component and the entire unit can then be placed on an H-rail.	47x12x18.1 (LxWxH)	170169	CP-TS-HS-35
	29.9	Cold rolled steel	Mounting accessories (set) for H-rail mounting. Is screwed onto the component and the entire unit can then be placed on an H-rail. Includes M4x10 screw (combi cross-slot screws).	49.1x13x8.7 (LxWxH) Material thickness: 2	527392	CPASC-BG-NRH
	8.8	Fine grained cold pressed steel	Mounting bracket for mounting valve terminals on even surfaces. Includes 2 M3x9 screws (2.5 A/F internal hexagon socket).	18 x 15 (LxW) Material thickness: 2	534416	VMPA-BG-RW
	–	Galvanised steel	Screw available as spare part, to DIN 912.	L: 45; Thread: M3	527643	M3x45

Accessories for valves and valve terminals VAME, mounting attachments


FESTO

Technical data

Mounting rail NR


Mounting rails for manifold mounting of components.

- G rail to DIN EN 50035
- H-rail to EN 60715




Dimensions

NRC-32-2000



Download CAD data → www.festo.com

NRH-35-2000



Ordering data

	Description	Length [m]	Product weight [g]	Material	Part No.	Type
	G-rail to DIN EN 50 035	2	1400	Galvanised steel	6756	NRC-32-2000
	H-rail to EN 60715	2	600	Galvanised steel	35430	NRH-35-2000¹⁾

1) Free of copper, PTFE and silicone

Festo - Your Partner in Automation



1 Festo Inc.
5300 Explorer Drive
Mississauga, ON L4W 5G4
Canada

Festo Customer Interaction Center
Tel: 1 877 463 3786
Fax: 1 877 393 3786
Email: customer.service.ca@festo.com



2 Festo Pneumatic
Av. Ceylán 3,
Col. Tequesquináhuac
54020 Tlalnepantla,
Estado de México

Multinational Contact Center
01 800 337 8669
ventas.mexico@festo.com



3 Festo Corporation
1377 Motor Parkway
Suite 310
Islandia, NY 11749

Festo Customer Interaction Center
1 800 993 3786
1 800 963 3786
customer.service.us@festo.com



4 Regional Service Center
7777 Columbia Road
Mason, OH 45040

Connect with us

www.festo.com/socialmedia



www.festo.com

Subject to change