


Connecting cables NEBV, for valves

Technical data

Connecting cable NEBV-H1G2

- Connecting cable for VUVG valves
- Pre-assembled
- Cable lengths 0.5 to 5 m
- For connecting to electrical connection box VAVE-L1-...H
- Suitable for valves with MH connection



General technical data		
Electrical connection		Socket, 2-pin
Nominal operating voltage	[V DC]	0 ... 30
Wire insulation colour code	Pin1	Red
	Pin3	Black
Type of mounting		Clip
Mounting position		Any
Protection class to EN 60529		IP40

Materials		
Type	NEBV-H1G2-KN	NEBV-H1G2-P
Housing	POM	POM
Housing colour	Black	Black
Pin contact	Tin-plated copper alloy	Tin-plated copper alloy
Cable sheath	–	PUR
Cable sheath colour	–	Grey
Insulating sheath	PVC	PVC
Cable properties	–	Suitable for use with energy chains
Note on materials	RoHS-compliant	RoHS-compliant



Operating and environmental conditions		
Ambient temperature	[°C]	–5 ... +60

Circuitry (view of socket)		
	Pin	Wire colour
	1	Red
	2	–
	3	Black

Connecting cables NEBV, for valves

Technical data

Dimensions Download CAD data → www.festo.com



Type	B1	H1	L1	L2
NEBV-H1G2-KN-0.5-N-LE2	8.3	8.4	500	13
NEBV-H1G2-KN-1-N-LE2			1000	
NEBV-H1G2-KN-2.5-N-LE2			2500	
NEBV-H1G2-KN-5-N-LE2			5000	

Type	B1	D1	H1	L1	L2	L3	L4
NEBV-H1G2-P-0.5-N-LE2	9	3.4	8.4	500	50	33.2	9
NEBV-H1G2-P-1-N-LE2				1000			
NEBV-H1G2-P-2.5-N-LE2				2500			
NEBV-H1G2-P-5-N-LE2				5000			

Ordering data						
Electrical connection	Cable composition	Product weight [g]	Length [m]	Part No.	Type	
Straight socket, 2-pin	2 individual cables	4	0.5	566654	NEBV-H1G2-KN-0.5-N-LE2	
		7	1	566655	NEBV-H1G2-KN-1-N-LE2	
		17	2.5	566656	NEBV-H1G2-KN-2.5-N-LE2	
		31	5	566657	NEBV-H1G2-KN-5-N-LE2	
	2-wire cable	8	0.5	566658	NEBV-H1G2-P-0.5-N-LE2	
		16	1	566659	NEBV-H1G2-P-1-N-LE2	
		35	2.5	566660	NEBV-H1G2-P-2.5-N-LE2	
		70	5	566661	NEBV-H1G2-P-5-N-LE2	

Festo - Your Partner in Automation



1 Festo Inc.
5300 Explorer Drive
Mississauga, ON L4W 5G4
Canada

Festo Customer Interaction Center
Tel: 1 877 463 3786
Fax: 1 877 393 3786
Email: customer.service.ca@festo.com



2 Festo Pneumatic
Av. Ceylán 3,
Col. Tequesquináhuac
54020 Tlalnepantla,
Estado de México

Multinational Contact Center
01 800 337 8669
ventas.mexico@festo.com



3 Festo Corporation
1377 Motor Parkway
Suite 310
Islandia, NY 11749

Festo Customer Interaction Center
1 800 993 3786
1 800 963 3786
customer.service.us@festo.com



4 Regional Service Center
7777 Columbia Road
Mason, OH 45040

Connect with us



www.festo.com/socialmedia



www.festo.com

Subject to change