


Mounting plates VN-T

FESTO



Mounting plates VN-T

Technical data

FESTO

Mounting plate VN-T...-NRH

for vacuum generator VN

➔ Internet: vn

for mounting on H-rail or via through-hole

Ambient temperature: 0 ... +60 °C

Material:



Plate VN-T2/T3/T4: POM reinforced

Plate VN-T6: PA reinforced

Slide: POM

RoHS-compliant

Free of copper and PTFE



Dimensions and ordering data											
Width [mm]	B1	D1	H1	L1	L2	L3	L4	L5	CRC ¹⁾	Weight [g]	Part No. Type
10	10.4	3.5	8	56.5	51	25.5	12.5	5.5	2	3.5	196951 VN-T2-BP-NRH
14	14.4		8	57.9	51.2	25.6	12.5	5.5	2	4.5	193641 VN-T3-BP-NRH
18	18.4	4.3	7.3	98	91	45.5	32.5	6.3	2	5.5	195279 VN-T4-BP-NRH
24	24									12.4	196956 VN-T6-BP-NRH

1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

Mounting plate VN-T

for vacuum generators VN-A/B/M

➔ Internet: vn


For wall mounting with through hole for housing type T3/T4

Material:

Plate: Galvanised steel

RoHS-compliant

Free of copper and PTFE



Dimensions and ordering data					
Width [mm]	B1	B2	CRC ¹⁾	Weight [g]	Part No. Type
14	13	4	2	4.8	547436 VN-T3-BP
18	17	6		6.4	547437 VN-T4-BP

1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

Festo - Your Partner in Automation



1 Festo Inc.
5300 Explorer Drive
Mississauga, ON L4W 5G4
Canada

Festo Customer Interaction Center
Tel: 1 877 463 3786
Fax: 1 877 393 3786
Email: customer.service.ca@festo.com



2 Festo Pneumatic
Av. Ceylán 3,
Col. Tequesquináhuac
54020 Tlalnepantla,
Estado de México

Multinational Contact Center
01 800 337 8669
ventas.mexico@festo.com



3 Festo Corporation
1377 Motor Parkway
Suite 310
Islandia, NY 11749

Festo Customer Interaction Center
1 800 993 3786
1 800 963 3786
customer.service.us@festo.com



4 Regional Service Center
7777 Columbia Road
Mason, OH 45040

Connect with us

www.festo.com/socialmedia



www.festo.com

Subject to change