














1 Basic Commissioning G120 with Festo three-phase asynchronous motor 690V/400V in delta connection









- Turn on DIN0 to measure the engine parameter. It takes round about 30sec
- Turn off DIN0 to save Data.

Now you are ready.

DIN0 -> ON/OFF

DIN1 -> LEFT/RIGHT

DIN3 -> Quit Error

ANA0 -> Desired speed