

Exhaust air flow control valve GRE-1/8

Part number: 10351

FESTO



Data sheet

Feature	Value
Valve function	Sound pressure control function
Selection of additional functions	With silencer
Pneumatic connection, port 1	G1/8
Adjustment component	Slotted head screw
Type of mounting	Screw-in
Standard nominal flow rate in flow control direction	520 l/min
Standard flow rate 0.6->0 MPa (6->0 bar, 87->0 psi)	0 l/min...520 l/min
Ambient temperature	-10 °C...70 °C
Mounting position	optional
Operating pressure complete temperature range	0 bar...10 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Media temperature	-10 °C...70 °C
Nominal torque	12 Nm
Tolerance for nominal tightening torque	± 20%
Product weight	15 g
Material screwed plug	Wrought aluminium alloy
Note on materials	RoHS-compliant
Material seals	NBR
Material adjusting screw	Brass