


# axial kit EAMM-A-D19-35S

Part number: 1087729

FESTO

Suitable for electric drives.



## Data sheet

Feature	Value
Assembly position	Any
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Transferable torque	1.1 Nm
Product weight	90 g
Interface code, actuator	D19A
Interface code, motor in	35S
Materials note	Contains PWIS substances Conforms to RoHS