


# ISO cylinder ESN-20- -P

Part number: 11655  
Product to be discontinued

FESTO

As per DIN ISO 6432, with elastic cushioning rings in end positions.  
Various mounting options, with or without additional mounting components.

Type to be discontinued. Available until 2018. See Support Portal for alternative products.



Exemplary representation

## Data sheet

Feature	Value
Stroke	1 ... 50 mm
Piston diameter	20 mm
Piston rod thread	M8
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Conforms to standard	CETOP RP 52 P ISO 6432
Piston-rod end	Male thread
Design structure	Piston Piston rod Cylinder barrel
Position detection	No
Variants	Single-ended piston rod
Operating pressure	1.2 ... 10 bar
Mode of operation	single-acting pushing action
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Ambient temperature	-20 ... 80 °C
Impact energy in end positions	0.2 J
Theoretical force at 6 bar, advance stroke	169 N
Moving mass with 0 mm stroke	186.8 g
Additional weight per 10 mm stroke	7.1 g
Basic weight for 0 mm stroke	200 g
Additional mass factor per 10 mm of stroke	7.2 g
Mounting type	with accessories
Pneumatic connection	G1/8
Materials note	Conforms to RoHS
Materials information for cover	Wrought Aluminium alloy neutral anodisation
Materials information for seals	NBR TPE-U(PU)
Materials information for piston rod	High alloy steel, non-corrosive
Materials information for cylinder barrel	High alloy steel, non-corrosive