


coupling EAMC-30-35-11-12

Part number: 123051

FESTO

For electromechanical drive with servomotor



Data sheet

| Feature | Value |
|------------------------|-----------------------|
| Holder diameter 1 | 11 mm |
| Holder diameter 2 | 12 mm |
| Size | 30 |
| Nominal length | 35 mm |
| Assembly position | Any |
| Max. speed | 8,000 1/min |
| Storage temperature | -25 ... 60 °C |
| Relative air humidity | 0 - 95 % |
| Ambient temperature | -25 ... 60 °C |
| Mass moment of inertia | 6.1 kgmm ² |
| Transferable torque | 9.2 Nm |
| Product weight | 45 g |
| Materials note | Conforms to RoHS |