

Push-in fitting QSM-M3-4-I-R-100

Part number: 132915

FESTO



Data sheet

Feature	Value
Size	Mini
Nominal size	1.5 mm
Type of seal on screwed plug	Sealing ring
Mounting position	optional
Design	Straight design, round releasing ring Push-pull principle
Size of pack	100
Operating pressure complete temperature range	-0.095 MPa...0.6 MPa -0.95 bar...6 bar -13.775 psi...87 psi
Temperature-dependent operating pressure	-0.095 MPa...1.4 MPa -0.95 bar...14 bar -13.775 psi...203 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...80 °C
Nominal torque	0.48 Nm
Tolerance for nominal tightening torque	± 55%
Product weight	2.2 g
Type of mounting	Internal hexagon, A/F 1.5 mm
Pneumatic connection, port 1	Male thread M3
Pneumatic connection, port 2	For tubing outside diameter of 4 mm
Colour of release ring	Blue
Note on materials	RoHS-compliant
Material housing	Nickel-plated steel
Material release ring	POM
Material tubing seal	NBR
Material tubing clamp component	High-alloy stainless steel