


Stepper motor EMMS-ST-87-S-SB-G2

Part number: 1370484

FESTO



Data sheet

Feature	Value
Ambient temperature	-10 °C...50 °C
Storage temperature	-20 °C...70 °C
Relative air humidity	0 - 85%
Conforms to standard	IEC 60034
Insulation protection class	B
Temperature class as per EN 60034-1	B
Rating class as per EN 60034-1	S1
Degree of protection	IP54
Electrical connector system	Plug
Note on materials	RoHS-compliant
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Approval	RCM trademark c UL us - Recognized (OL)
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Nominal operating voltage DC	48 V
Motor holding torque	2.5 Nm
Max. rotational speed	2130 rpm
Stepper angle for complete step	1.8 deg
Stepping angle tolerance	±5%
Nominal motor current	9.5 A
Voltage constant, phase	19 mVmin
Phase winding resistance	0.1 Ohm
Phase winding inductance	0.45 mH
Mass moment of inertia of rotor	1 kgcm ²
Total mass moment of inertia of output	1.07 kgcm ²
Product weight	2350 g
Permissible axial shaft load	65 N
Permissible radial shaft load	200 N

Feature	Value
Brake holding torque	2 Nm
Operating voltage DC for brake	24 V
Power consumption, brake	11 W
Mass moment of inertia of brake	0.07 kgcm ²