


Flat cylinder DZH-63-125-PPV-A

Part number: 14079

FESTO



Data sheet

| Feature | Value |
|--|--|
| Stroke | 125 mm |
| Piston diameter | 63 mm Equivalent diameter |
| Torsional backlash at piston rod +/- | 0.67 deg |
| Cushioning | Pneumatic cushioning, adjustable at both ends |
| Mounting position | optional |
| Mode of operation | Double-acting |
| Design | Piston Piston rod |
| Position detection | Via proximity switch |
| Protection against torque/guide | Oval piston |
| Operating pressure | 0.06 MPa...1 MPa 0.6 bar...10 bar |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Ambient temperature | -20 °C...80 °C |
| Cushioning length | 23 mm |
| Max. torque for protection against torsion | 2 Nm |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke | 1682 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 1870 N |
| Additional weight per 10 mm stroke | 80 g |
| Basic weight for 0 mm stroke | 1690 g |
| Type of mounting | Via female thread With accessories Either: |
| Pneumatic connection | G3/8 |
| Note on materials | RoHS-compliant |
| Material cover | Aluminium |
| Material seals | TPE-U(PU) |
| Material housing | Aluminium |

| Feature | Value |
|---------------------|------------------|
| Material piston rod | High-alloy steel |