

ISO cylinder DSBC-100- -PPVA-N3

Part number: 1463598

FESTO



Data sheet

| Feature | Value |
|--|--|
| Stroke | 1 mm...2800 mm |
| Piston diameter | 100 mm |
| Piston rod thread | M20x1.5 |
| Cushioning | Pneumatic cushioning, adjustable at both ends |
| Mounting position | optional |
| Conforms to standard | ISO 15552 |
| Piston-rod end | Male thread |
| Design | Piston Piston rod Profile barrel |
| Position detection | Via proximity switch |
| Variants | Piston rod at one end |
| Operating pressure | 0.04 MPa...1.2 MPa 0.4 bar...12 bar |
| Mode of operation | Double-acting |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -20 °C...80 °C |
| Impact energy in end positions | 2.5 J |
| Cushioning length | 31 mm |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke | 4418 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 4712 N |
| Moving mass for 0 mm stroke | 1000 g |
| Additional moving mass per 10 mm stroke | 39 g |
| Basic weight for 0 mm stroke | 3665 g |
| Additional weight per 10 mm stroke | 101 g |
| Type of mounting | Via female thread With accessories Either: |
| Pneumatic connection | G1/2 |

| Feature | Value |
|---------------------------|---|
| Note on materials | RoHS-compliant |
| Material cover | Die-cast aluminium, coated |
| Material piston seal | TPE-U(PU) |
| Material piston | Wrought aluminium alloy |
| Material piston rod | High-alloy steel |
| Material piston rod wiper | TPE-U(PU) |
| Buffer seal material | TPE-U(PU) |
| Cushioning boss material | POM |
| Material cylinder barrel | Smooth-anodised wrought aluminium alloy |
| Material nut | Galvanised steel |
| Material bearing | POM |
| Material collar screws | Galvanised steel |