


# Motor flange EAMF-A-38A-40G

Part number: 1460097

FESTO



## Data sheet

Feature	Value
Mounting position	optional
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Ambient temperature	-10 °C...60 °C
Product weight	148 g
Interface code, motor in	40G
Interface code, clutch housing	38A
Note on materials	RoHS-compliant