

**FRC-3/8-S-7-B**

Service unit

Data sheet

Part no.: 150067

Page:1

<b>Feature</b>	<b>Data/description</b>
Modular design	<b>Yes</b>
Input pressure 1 min. (bar)	<b>0,5 bar</b>
Input pressure 1 max. (bar)	<b>14 bar</b>
Output pressure 2 max.	<b>7 bar</b>
Thread for port 1	<b>G 3/8</b>
Thread for port 2	<b>G 3/8</b>
Type of mounting	<b>Hole</b>
Minimum ambient temperature	<b>-10 °C</b>
Maximum ambient temperature	<b>60 °C</b>
Minimum medium temperature	<b>-10 °C</b>
Maximum medium temperature	<b>60 °C</b>
Minimum flow for lubricator operation	<b>25 l/min</b>
Design lubricator	<b>Direct proportional</b>
Oil capacity max.	<b>90 cm<sup>3</sup></b>
Oil viscosity	<b>23</b>
Metal bowl guard	<b>No</b>
Grade of filtration	<b>40 µm</b>
Maximum condensate capacity	<b>50 cm<sup>3</sup></b>
Condensate drain system	<b>Manual, rotary</b>
Actuator locking (press. reg.)	<b>Pull-up-and-turn adjustment</b>
Pressure hysteresis (pressure regul.)	<b>0,5 bar</b>
Pressure gauge yes/no	<b>Yes</b>
Material of housing	<b>PA-polymer</b>
Material of bowl	<b>PA-polymer</b>
Contains silicone materials	<b>Yes</b>
Standard nominal flow rate 1-2	<b>1700 l/min</b>
Operating medium input 1	<b>Compressed air</b>
Operating medium output 2	<b>Compressed air, filtered 40 µm, lubricated</b>