

Motor controller CMMP-AS-C10-11A-P3-M3

Part number: 1501328

FESTO



Data sheet

Feature	Value
Type of mounting	On sub-base Screw-clamped
Product weight	3450 g
Display	7-segment display
Approval	RCM trademark c UL us listed (OL)
CE mark (see declaration of conformity)	To EU EMC Directive To EC Machinery Directive To EU Low Voltage Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK regulations for machines To UK RoHS instructions To UK regulations for electrical equipment
Storage temperature	-25 °C...70 °C
Ambient temperature	0 °C...40 °C
Relative air humidity	0 - 90%
Degree of protection	IP10 IP20
Pollution degree	2
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364 zone III
Phases of nominal operating voltage	3-phase
Nominal operating voltage AC	400 V
Permissible voltage fluctuations	+/- 10 %
Mains frequency	50 Hz...60 Hz
Nominal current	11 A
Mains filter	Integrated
Max. intermediate circuit voltage DC	560 V
Brake resistance	68 Ohm
Pulse power, brake resistance	8.5 kVA
Nominal voltage for logic power supply DC	24 V
Permissible range for logic voltage	± 20 %
Current consumption of logic power supply without clamping brake	1 A

Feature	Value
Output voltage class AC	3x 0 - 360 V
Nominal output current	10 A
Nominal current per phase, effective	10 A
Peak current per phase, effective	20 A
Max. peak current duration	5 s
Controller nominal output	6000 VA
Maximum output	12000 VA
Output frequency	0 Hz...1000 Hz
Parameterisation interface	Parameterisation and commissioning USB Ethernet
Fieldbus link	CANopen DeviceNet EtherCAT EtherNet/IP Modbus/TCP PROFINET Profibus DP
Communication profile	DS301/DSP402 FHPP
Process interfacing	I/O coupling For 256 position sets
Max. fieldbus transmission rate	1 Mbit/s
Bus connection	Plugs 9-pin Sub-D
Encoder interface output, features	Resolution 16384 ppr
Encoder interface output, function	Actual value feedback via encoder signals in speed control mode. Setpoint specification for downstream slave drive.
Encoder interface input, features	3-phase encoder signals EnDat HIPERFACE RS422 SINCOS
Encoder interface input, function	Setpoint speed value as encoder signal Specifies the speed of the slave drive in synchronous mode.
Number of digital logic inputs	10
Features of logic input	Galvanically isolated Freely configurable
Working range of logic input	8 V...30 V
Number of digital logic outputs 24 V DC	5
Features of digital logic outputs	Galvanically isolated Freely configurable in some cases
Max. current digital logic outputs	100 mA
Number of analogue setpoint inputs	2
Features of setpoint inputs	Differential inputs Configurable for speed Configurable for current
Working range setpoint input	± 10 V
Impedance of setpoint input	20 kOhm
Number of analogue monitor outputs	2
Working range of monitor outputs	± 10 V
Resolution of monitor outputs	9 bit
Features of monitor outputs	Short-circuit proof