


Proximity sensor SMT0-4U-NS-S-LED-24

Part number: 152743

FESTO



Data sheet

Feature	Value
Design	Round
Based on standard	EN 60947-5-2
Approval	RCM trademark
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Note on materials	RoHS-compliant
Measured variable	Position
Measuring principle	Magneto-inductive
Ambient temperature	-25 °C...70 °C
Repetition accuracy	0.2 mm
Switching output	NPN
Switching element function	N/O contact
Switch-on time	0.5 ms
Switch-off time	0.5 ms
Max. output current	200 mA
Max. switching capacity DC	6 W
Voltage drop	2 V
Inductive protective circuit	Integrated
Min. load current	0.1 mA
Off-state current	0.01 mA
Short circuit current rating	Pulsed
Overload protection	Available
Operational voltage range DC	10 V...30 V
Residual ripple	10 %
Reverse polarity protection	For all electrical connections
Electrical connection 1, connection type	Plugs
Electrical connection 1, connector system	M8x1, A-coded, to EN 61076-2-104
Electrical connection 1, number of connections/cores	3
Electrical connection 1, type of mounting	Screw-type lock
Connection outlet orientation	In-line

Feature	Value
Material electrical contact	Gold-plated brass
Type of mounting	With accessories
Max. tightening torque	0.8 Nm
Mounting position	optional
Product weight	6 g
Housing colour	Black
Material housing	PA PET PUR
Switching status indication	Yellow LED
Degree of protection	IP67
LABS (PWIS) conformity	VDMA24364-B2-L