

# Condensate drain WA-2

Part number: 152810

FESTO



## Data sheet

| Feature                     | Value                                 |
|-----------------------------|---------------------------------------|
| Type of actuation           | Mechanical                            |
| Mounting position           | Vertical +/-5°                        |
| Manual override             | Non-detenting                         |
| Condensate drain            | Fully automatic                       |
| Design                      | External, mechanical, fully automatic |
| Measured variable           | Level                                 |
| Valve function              | 2/2 open, single solenoid             |
| Operating pressure          | 1.5 bar...14 bar                      |
| Operating medium            | Water                                 |
| LABS (PWIS) conformity      | VDMA24364 zone III                    |
| Storage temperature         | -20 °C...60 °C                        |
| Media temperature           | 0 °C...50 °C                          |
| Ambient temperature         | 0 °C...50 °C                          |
| Product weight              | 92 g                                  |
| Type of mounting            | In-line installation                  |
| Condensate drain connection | PK-4                                  |
| Pneumatic connection        | M9                                    |
| Material housing            | Wrought aluminium alloy               |