


servo motor EMMS-AS-190-SK-HS-AS

Part number: 1584915
Product to be discontinued

FESTO

Without gear unit.



Data sheet

| Feature | Value |
|--|--|
| Ambient temperature | -10 ... 40 °C |
| Storage temperature | -20 ... 60 °C |
| Relative air humidity | 0 - 90 % |
| Conforms to standard | IEC 60034 |
| Insulation protection class | F |
| Rating class according to EN 60034-1 | S1 |
| Temperature monitoring | PTC resistor |
| Protection class | IP54 |
| Shaft design Featherkey | DIN 6885 A 10 x 8 x 40 |
| Electrical connector system | Plug |
| Materials note | Conforms to RoHS |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity | VDMA24364-B2-L |
| Authorisation | RCM Mark c UL us - Recognized (OL) |
| CE mark (see declaration of conformity) | to EU directive for EMC to EU directive low-voltage devices in accordance with EU RoHS directive |
| UKCA marking (see declaration of conformity) | To UK instructions for electrical equipment To UK instructions for EMC To UK RoHS instructions |
| Nominal operating voltage DC | 565 V |
| Nominal voltage DC | 565 V |
| Type of winding switch | Star inside |
| Number of pole pairs | 6 |
| Standstill torque | 26.2 Nm |
| Nominal torque | 17.47 Nm |
| Peak torque | 80 Nm |
| Nominal rotary speed | 3,000 1/min |
| Max. speed | 5,300 1/min |
| Nominal motor power | 5,490 W |
| Nominal motor current | 14.43 A |
| Peak current | 77.2 A |
| Motor constant | 1.211 Nm/A |
| Voltage constant, phase-to-phase | 75.4 mV/min |
| Phase-phase winding resistance | 0.283 Ohm |
| Phase-phase winding inductance | 3.07 mH |
| Overall mass moment of inertia at power take-off | 51.9 kgcm ² |
| Product weight | 20,860 g |
| Permissible axial shaft load | 250 N |
| Permissible radial shaft load | 940 N |
| Rotor position sensor | Absolute single turn encoder |
| Rotary position encoder interface | EnDat 21 |

| Feature | Value |
|---|------------------------------------|
| Rotary position encoder measuring principle | Inductive |
| Rotor position encoder resolution | 18 Bit |
| MTTF, subcomponent | 76 years, rotary position encoder |
| MTTFd, subcomponent | 152 years, rotary position encoder |
| Energy efficiency | ENEFF (CN) / Class 2 |