

ESN-8--P-S3

Standard cylinder

Data sheet

Part no.: 158890

Page:1

Feature	Data/description
Mode of operation	Single, pushing
Shape piston	Round
Shape of piston rod	Round
In accordance with standard ISO	ISO 6432
Sensing type	None
Type of cushioning	Internal cushioning ring (non-adjustable)
Protection against torsion	None
Piston, nominal size	8
X-stroke	X
Min. stroke for X-stroke	1 mm
Max. stroke for X-stroke	50 mm
Piston rod diameter	4 mm
End of piston rod	Male thread
KK Piston rod thread	M 4
Operating pressure min.	1,2 bar
Operating pressure max.	10 bar
Minimum ambient temperature	-20 °C
Maximum ambient temperature	80 °C
Bearing cap connection type	Female thread
EE Connecting thread for bearing cap	M 5
Material of cap	Wrought aluminium alloy
Material of seals	FPM, TPE-U(PU)
Material of piston rod	Stainless high-alloy steel
Material of barrel/housing	Stainless high-alloy steel
Coating of cover	Neutral anodised
Air connection type cover cap	Female thread
EE Connecting thread for end cap	M 5
Effective force (theor.) at 6 bar, adv.	24,6 N
Spring return force max.	5,4 N
Air consumption at 6 bar advance /10mm	0,0032 l
Medium	Dried air, lubricated or unlubricated