


Lubricator LOE-1/2-D-MIDI

Part number: 159587

FESTO



Data sheet

Feature	Value
Size	Midi
Series	D
Mounting position	Vertical +/-5°
Design	Proportional standard mist lubricator
Max. oil capacity	110 cm ³
Bowl guard	Metal bowl guard
Operating pressure	0 MPa...1.6 MPa 0 bar...16 bar 0 psi...232 psi
Min. flow rate for lubricator function	8 l/min
Standard nominal flow rate (standardised to DIN 1343)	6100 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4] Inert gases
Note on operating and pilot medium	Lubricated operation not possible
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C...60 °C
Air purity class at output	Compressed air to ISO 8573-1:2010 [7:4:-] Inert gases
Media temperature	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Product weight	630 g
Type of mounting	With accessories
Pneumatic connection, port 1	G1/2
Pneumatic connection, port 2	G1/2
Note on materials	RoHS-compliant
Material bowl	PC