


Air reservoir CRVZS-10

Part number: 160237

FESTO



Data sheet

Feature	Value
Volume	10 l
Mounting position	Condensate drain underneath
Conforms to standard	AD 2000
Operating pressure	-0.095 MPa...1.6 MPa -0.95 bar...16 bar -13.78 psi...232 psi
Approval	German Technical Control Board (TÜV)
CE mark (see declaration of conformity)	In accordance with EU Pressure Equipment Directive
UKCA marking (see declaration of conformity)	to UK Pressure Equipment Regulations
Operating medium	Compressed air to ISO 8573-1:2010 [-::-] Nitrogen
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Suitable for use with food	See supplementary material information
Media temperature	-10 °C...100 °C
Ambient temperature	-10 °C...100 °C
Max. tightening torque for connecting thread	130 Nm
Max. tightening torque for condensate drain	27 Nm
Product weight	6459 g
Type of mounting	With through-hole
Condensate drain connection	G3/8
Pneumatic connection	G1
Note on materials	RoHS-compliant
Material air reservoir	High-alloy stainless steel