

Compact cylinder AEVUZ-1/2"- -P-A


Part number: 160620

FESTO

For proximity sensing, piston-rod end with female thread.

This product is only available if ordered from the Festo Corporation, USA.

Products to be discontinued. Available until 2011.



Exemplary representation



Data sheet

Feature	Value
Stroke	0.2 ... 0.4 "
Piston diameter	1/2"
Cushioning	P: Flexible cushioning rings/plates at both ends
Mode of operation	single-acting pulling action
Piston-rod end	Female thread
Operating pressure	21.8 ... 145 Psi
Operating medium	Filtered compressed air
Corrosion resistance classification CRC	2
Ambient temperature	-4 ... 176 °F
Theoretical force at 6 bar, advance stroke	42 N
Moving mass with 0 mm stroke	8 g
Additional weight per 10 mm stroke	2 g
Basic weight for 0 mm stroke	87 g
Additional mass factor per 10 mm of stroke	59 g
Pneumatic connection	UNF10-32
Operating pressure [psi]	21.8 ... 145 psi
Materials information for cover	Wrought Aluminium alloy
Materials information for dynamic seals	TPE-U(PU) NBR
Materials information for piston rod	High alloy steel, non-corrosive
Materials information for cylinder barrel	Wrought Aluminium alloy