

Trunnion support CRLNZG-40/50

Part number: 161875

FESTO



Data sheet

Feature	Value
Size	40/50
Based on standard	ISO 15552
Corrosion resistance class CRC	4 - Very high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Product corresponds to the internal product definition from Festo for use in battery production: Metals with more than 1% by mass of copper, zinc or nickel are excluded from use. The exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Ambient temperature	-40 °C...150 °C
Max. load capacity	2.5 kN
Product weight	323 g
Note on materials	RoHS-compliant
Material mounting	High-alloy stainless steel
Material bearing	Polymer