



DSW-50-100-P-B

Round cylinder

| Feature | Data/description |
|--|--|
| Stroke | 100 mm |
| Piston diameter | 50 mm |
| Cushioning | Flexible cushioning rings or plates at both ends (P) |
| Assembly position | Any |
| Conforms to standard | ISO 6431 |
| Design structure | Piston Piston rod Cylinder barrel |
| Position detection | none |
| Variants | Single-ended piston rod |
| Operating pressure | 1 - 10 bar |
| Mode of operation | double-acting |
| Operating medium | Dried compressed air, lubricated or unlubricated |
| Corrosion resistance classification CRC | 2 |
| Ambient temperature | -20 - 80 °C |
| Theoretical force at 6 bar, return stroke | 990 N |
| Theoretical force at 6 bar, advance stroke | 1.178 N |
| Additional weight per 10 mm stroke | 35 g |
| Basic weight for 0 mm stroke | 1.277 g |
| Mounting type | with accessories |
| Pneumatic connection | G1/4 |
| Materials information for cover | Wrought Aluminium alloy |
| Materials information for seals | TPE-U(PU) NBR |

**DSW-50-100-P-B****Round cylinder**

| Feature | Data/description |
|--------------------------------------|---------------------------------|
| Materials information, housing | High alloy steel, non-corrosive |
| Materials information for piston rod | High alloy steel |