



DSW-63-40-PPV-A-B

Round cylinder

| Feature | Data/description |
|--|---|
| Stroke | 40 mm |
| Piston diameter | 63 mm |
| Cushioning | Pneumatic cushioning, adjustable at both ends (PPV) |
| Assembly position | Any |
| Conforms to standard | ISO 6431 |
| Design structure | Piston Piston rod Cylinder barrel |
| Position detection | with proximity sensor |
| Variants | Single-ended piston rod |
| Operating pressure | 1 - 10 bar |
| Mode of operation | double-acting |
| Operating medium | Dried compressed air, lubricated or unlubricated |
| Corrosion resistance classification CRC | 2 |
| Ambient temperature | -20 - 80 °C |
| Cushioning length | 27 mm |
| Theoretical force at 6 bar, return stroke | 1.682 N |
| Theoretical force at 6 bar, advance stroke | 1.870 N |
| Additional weight per 10 mm stroke | 41 g |
| Basic weight for 0 mm stroke | 1.738 g |
| Mounting type | with accessories |
| Pneumatic connection | G3/8 |
| Materials information for cover | Wrought Aluminium alloy |
| Materials information for seals | TPE-U(PU) |

**DSW-63-40-PPV-A-B****Round cylinder**

| Feature | Data/description |
|--------------------------------------|---------------------------------|
| | NBR |
| Materials information, housing | High alloy steel, non-corrosive |
| Materials information for piston rod | High alloy steel |