

CPE10-M1H-5LS-QS-6

Solenoid valve

Data sheet

Part no.: 162897

Page:1

Feature	Data/description
Switching function	5/2-way valve
Switching function short code	5/2
Direction of flow reversible	Yes
Operating principle	Slide
Shape of function component	Piston
With exhaust flow control	Yes
Type of regulation	Indirect
Control type	Monostable
Type of reset	Air spring
External auxiliary pilot air	Yes
Type of mounting	Screw
Installation position	Any
Nominal size	4 mm
Operating pressure min.	-0,9 bar
Operating pressure max.	10 bar
Minimum ambient temperature	-10 °C
Maximum ambient temperature	50 °C
Minimum medium temperature	-10 °C
Maximum medium temperature	50 °C
Min. pilot pressure	2,5 bar
Pilot pressure max.	8 bar
Type of connection, air supply	Push-in
Nominal size of tubing connection, suppl	6
Air connection type power port	Push-in
Nominal size of tubing connection, worki	6
Air connection type aux. pilot air suppl	Push-in
Nom. size aux. pilot air supply	3
Air connection type aux. pilot air exhau	Thread
Connecting thread for aux. pilot air exh	M 3
Type pilot control air Supply and exhaus	External pilot air, ducted pilot exhaust
Actuation/reset	Single solenoid, air spring return

CPE10-M1H-5LS-QS-6

Solenoid valve

Data sheet

Part no.: 162897

Page:2

Feature	Data/description
Manual override	Non-detenting (detenting with attachment)
Operating status display	No
Product weight	0,056 kg
Country-specific approval certificate (U	c UL us (OL)
Standard nominal flow rate 1 - 2	320 l/min
Standard nominal flow rate 2 - 3	320 l/min
Standard nominal flow rate 1 - 4	320 l/min
Standard nominal flow rate 4 - 3/5	320 l/min
Response time OFF/OVER (dom.)	15 ms
Response time OFF/OVER	23 ms
Voltage type	DC
Nominal voltage	24 V
Power consumption (DC)	1 W
Medium	Compressed air, filtered 40 µm (may be lubricated)
Degree of protection	IP65