

**PAN-L-4x0,75-NT****Plastic tubing**

<b>Feature</b>	<b>Data/description</b>
Ambient temperature	-30 - 80 °C
Operating medium	Filtered compressed air Vacuum
Shore hardness	55 +/- 3
Colour	neutral
Inside diameter	2,900 mm
Outside diameter	4,000 mm
Food-industry approval	90/128/EWG
Materials note	Copper and PTFE-free
Product weight according to length	0,0060 kg/m
Min. bending radius	18,000 mm
Materials information for tubing	TPE-A