

CPE10-M1H-3OLS-M5

Solenoid valve

Data sheet

Part no.: 162883

Page:1

Feature	Data/description
Switching function	3/2-way valve, normally open
Switching function short code	3/2
Direction of flow reversible	No
Operating principle	Slide
Shape of function component	Piston
With exhaust flow control	No
Type of regulation	Indirect
Control type	Monostable
Type of reset	Air spring
External auxiliary pilot air	Yes
Type of mounting	Screw
Installation position	Any
Nominal size	4 mm
Operating pressure min.	-0,9 bar
Operating pressure max.	10 bar
Minimum ambient temperature	-10 °C
Maximum ambient temperature	50 °C
Minimum medium temperature	-10 °C
Maximum medium temperature	50 °C
Min. pilot pressure	2,5 bar
Pilot pressure max.	8 bar
Type of connection, air supply	Female thread
Connecting thread, supply port	M 5
Air connection type power port	Female thread
Connecting thread, working port	M 5
Type of connection, exhaust	Female thread
Connecting thread, exhaust port	M 5
Air connection type aux. pilot air suppl	Female thread
Connecting thread for aux. pilot air sup	M 3
Air connection type aux. pilot air exhau	Female thread
Connecting thread for aux. pilot air exh	M 3

CPE10-M1H-3OLS-M5

Solenoid valve

Data sheet

Part no.: 162883

Page:2

Feature	Data/description
Type pilot control air Supply and exhaust	External pilot air and air spring, ducted pilot exhaust
Actuation/reset	Single solenoid, air spring return
Manual override	Non-detenting (detenting with attachment)
Operating status display	No
Product weight	0,04 kg
Country-specific approval certificate (UL)	c UL us (OL)
Standard nominal flow rate 1 - 2	190 l/min
Standard nominal flow rate 2 - 3	190 l/min
Standard nominal flow rate 1 - 4	190 l/min
Standard nominal flow rate 4 - 3/5	190 l/min
Response time OFF/OVER (dom.)	18 ms
Response time OFF/OVER	14 ms
Voltage type	DC
Nominal voltage	24 V
Power consumption (DC)	1 W
Medium	Compressed air, filtered 40 µm (may be lubricated)
Degree of protection	IP65