

Swivel module DSM-12-270-P-CL

Part number: 164321

FESTO

With spigot shaft, shock absorber on left

These drives can be delivered on request with ATEX certification. The data on "ATEX identification", "ATEX ambient temperature" and "CE label" in the data sheet relate only to drives with certification.



Data sheet

| Feature | Value |
|-----------------------------------------|-----------------------------------------------------------------------------|
| Size | 12 |
| Cushioning angle | 13 deg |
| Rotation angle adjustment range | 0 ... 254 deg |
| Swivel angle | 254 deg |
| Cushioning | CL: shock absorber left P: Flexible cushioning rings/plates at both ends |
| Assembly position | Any |
| Fine adjustment | -5 deg |
| Mode of operation | double-acting |
| Design structure | Rotary vane |
| Position detection | No |
| Operating pressure | 2 ... 10 bar |
| Max. swivel frequency at 6 bar | 1.5 Hz |
| ATEX identification | II 2 G c T4 |
| ATEX ambient temperature | 0°C ≤ Ta ≤ +60°C |
| Operating medium | Filtered compressed air |
| CE mark (see declaration of conformity) | to EU directive explosion protection (ATEX) |
| Ambient temperature | -10 ... 60 °C |
| Torque at 6 bar | 1.25 Nm |
| Product weight | 300 g |
| Mounting type | with internal (female) thread |
| Pneumatic connection | M5 |
| Materials note | Free of copper and PTFE |
| Materials information for drive shaft | Steel Nickel plated |
| Materials information for seals | TPE-U(PU) |
| Materials information, housing | Wrought Aluminium alloy |