


Intermediate ILR-03-ZP-P-4,0

Part number: 164941

FESTO



Datasheet

Feature	Value
Image code	F10
Design regulating valve	piston
Type of pilot control	Direct
Behaviour during flow reversal	Non-return valve
Control direction	I->II
Modular design	Yes
Supply pressure I min.	0 bar
Supply pressure I max.	10 bar
Output pressure II min.	0 bar
Output pressure II max.	8 bar
Connection type I	Sub-base
Connection type II	Sub-base
Installation position	certain
Type of mounting	Screw-in
Length	194,7 mm
Length	106,8 mm
Total height	30,5 mm
Total width	17,5 mm
Minimum ambient temperature	-10 °C
Maximum ambient temperature	60 °C
Minimum temperature of medium	-10 °C
Maximum temperature of medium	60 °C
Pressure gauge yes/no	No
Number pressure gauge connections	1
Thread type pressure gauge thread	M
Thread diameter (metric)	3 mm
Distance	20,5 mm
Material of seals	NBR-Elastomer
Silicone status	Free
Standard nominal flow rate I-II	180 l/min
Medium of operation	Filtered compressed air (40 µm)
Leakage	3 l/h