

# guided drive DFM-12-25-P-A-GF

Part number: 170826

★ Core product range

FESTO

With integrated guide.

The proximity switch, type SMTSO-8E, can be used with this product with stroke lengths of 20 to 40 mm only when the corresponding mounting kit, type SMB-8E, is mounted outwardly.



## Data sheet

Feature	Value
Centre of gravity distance from working load to yoke plate	25 mm
Stroke	25 mm
Piston diameter	12 mm
Operating mode of drive unit	Yoke
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Guide	Plain-bearing guide
Design structure	Guide
Position detection	For proximity sensor
Operating pressure MPa	0.2 ... 1 MPa
Operating pressure	2 ... 10 bar
Max. speed	0.8 m/s
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 ... 80 °C
Impact energy in end positions	0.07 Nm
Max. force F <sub>y</sub>	240 N
Max. force F <sub>y</sub> static	240 N
Max. force F <sub>z</sub>	240 N
Max. force F <sub>z</sub> static	240 N
Max. torque M <sub>x</sub>	4.92 Nm
Max. torque M <sub>x</sub> static	4.92 Nm
Max. torque M <sub>y</sub>	2.06 Nm
Max. torque M <sub>y</sub> static	2.06 Nm
Max. torque M <sub>z</sub>	2.06 Nm
Max. torque M <sub>z</sub> static	2.06 Nm
Max. permissible torque load M <sub>x</sub> as a function of the stroke	0.68 Nm
Max. useful load as a function of the stroke at defined distance x <sub>s</sub>	23 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting	51 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	68 N
Moving mass	193 g
Product weight	411 g
alternative connections	See product drawing
Pneumatic connection	M5
Materials note	Conforms to RoHS
Material cover	Wrought Aluminium alloy
Material seals	NBR
Material housing	Wrought Aluminium alloy
Material piston rod	High alloy steel, non-corrosive