



round cylinder DSAG-10- -PPV-S2

Part number: 171349
Product to be discontinued

FESTO

End cap with threaded lug, with through piston rod
Type to be discontinued. Available until 2024. See Support Portal for alternative products.



Exemplary representation

Data sheet

Feature	Value
Stroke	1 ... 160 mm
Piston diameter	10 mm
Piston rod thread	M4
Cushioning	PPV: Pneumatic cushioning adjustable at both ends
Piston-rod end	Male thread
Operating pressure	1 ... 10 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-20 ... 80 °C
Cushioning length	9.5 mm
Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting	39.6 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	47.1 N
Moving mass with 0 mm stroke	11.1 g
Additional mass factor per 10 mm of stroke	1 g
Basic weight for 0 mm stroke	19 g
Additional weight per 10 mm stroke	2.7 g
Pneumatic connection	M8x1
Material cover	Wrought Aluminium alloy
Material seals	NBR TPE-U(PU)
Material housing	High alloy steel, non-corrosive
Material piston rod	High alloy steel, non-corrosive