


round cylinder DSAS-32- -P-A

Part number: 172080
Product to be discontinued

FESTO

End cap with swivel bearing

Type to be discontinued. Available until 2024. See Support Portal for alternative products.



Exemplary representation

Data sheet

| Feature | Value |
|--|---|
| Stroke | 1 ... 500 mm |
| Piston diameter | 32 mm |
| Cushioning | P: Flexible cushioning rings/plates at both ends |
| Operating pressure | 1 ... 10 bar |
| Mode of operation | double-acting |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity | VDMA24364-B2-L |
| Ambient temperature | -20 ... 80 °C |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting | 415 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance | 483 N |
| Moving mass with 0 mm stroke | 222 g |
| Additional mass factor per 10 mm of stroke | 8.9 g |
| Basic weight for 0 mm stroke | 312 g |
| Additional weight per 10 mm stroke | 15.4 g |
| Pneumatic connection | M26x1,5 |
| Material cover | Wrought Aluminium alloy |
| Material seals | NBR TPE-U(PU) |
| Material housing | High alloy steel, non-corrosive |
| Material piston rod | High alloy steel, non-corrosive |