



# round cylinder DSAG-40- -P-A-S2

Part number: 172448  
Product to be discontinued

FESTO

End cap with threaded lug, with through piston rod  
Type to be discontinued. Available until 2024. See Support Portal for alternative products.



Exemplary representation

## Data sheet

Feature	Value
Stroke	1 ... 500 mm
Piston diameter	40 mm
Piston rod thread	M12x1,25
Cushioning	P: Flexible cushioning rings/plates at both ends
Piston-rod end	Male thread
Operating pressure	1 ... 10 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-20 ... 80 °C
Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting	633.1 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	754.1 N
Moving mass with 0 mm stroke	469 g
Additional mass factor per 10 mm of stroke	15.9 g
Basic weight for 0 mm stroke	586 g
Additional weight per 10 mm stroke	24 g
Pneumatic connection	M32x2
Material cover	Wrought Aluminium alloy
Material seals	NBR TPE-U(PU)
Material housing	High alloy steel, non-corrosive
Material piston rod	High alloy steel