



Data sheet

Part no.: **174822**

Page:1

## HMP-16-- Linear module

Feature	Data/description
Mode of operation	double-acting
Operating mode of drive unit	Yoke
Piston diameter	16 mm
Ambient temperature	0 - 60 °C
Position detection	with proximity sensor
Operating pressure	4,000 - 8,000 bar
Theoretical force at 6 bar, advance stroke	121,000 N
Theoretical force at 6 bar, return stroke	104,000 N
Operating medium	Filtered compressed air
Corrosion resistance classification CRC	2
Protection against torque/guide	Guide rod with yoke