


coupling EAMC-65-90-20-25

Part number: 176035

FESTO

For DGE.



Data sheet

| Feature | Value |
|------------------------|-----------------------|
| Holder diameter 1 | 20 mm |
| Holder diameter 2 | 25 mm |
| Size | 65 |
| Nominal length | 90 mm |
| Assembly position | Any |
| Max. speed | 4,500 1/min |
| Storage temperature | -25 ... 60 °C |
| Relative air humidity | 0 - 95 % |
| Ambient temperature | -25 ... 60 °C |
| Mass moment of inertia | 417 kgmm ² |
| Transferable torque | 85 Nm |
| Product weight | 535 g |
| Materials note | Conforms to RoHS |