


Round cylinder DSAQ-32- -PPV-A-S6

Part number: 176452


FESTO

End cap with air connection perpendicular to cylinder axis, with heat resistant seals to 120 °C

This product is only available if ordered from Festo Korea Co. Ltd.



Exemplary representation



Data sheet

Feature	Value
Stroke	1 ... 500 mm
Piston diameter	32 mm
Cushioning	PPV: Pneumatic cushioning adjustable at both ends
Operating pressure	1 ... 10 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2
Ambient temperature	-20 ... 120 °C
Cushioning length	19 mm
Theoretical force at 6 bar, return stroke	415 N
Theoretical force at 6 bar, advance stroke	483 N
Moving mass with 0 mm stroke	222 g
Additional weight per 10 mm stroke	15.4 g
Basic weight for 0 mm stroke	312 g
Additional mass factor per 10 mm of stroke	8.9 g
Pneumatic connection	M26x1,5
Materials information for cover	Wrought Aluminium alloy
Materials information for seals	FPM
Materials information, housing	High alloy steel, non-corrosive
Materials information for piston rod	High alloy steel, non-corrosive