



standards-based cylinder DSBF-C-50- -PPVA-N3-R

Part number: 1774418

FESTO



Exemplary representation



Data sheet

| Feature | Value |
|--|---|
| Stroke | 1 ... 2,800 mm |
| Piston diameter | 50 mm |
| Piston rod thread | M16x1,5 |
| Cushioning | PPV: Pneumatic cushioning adjustable at both ends |
| Assembly position | Any |
| Conforms to standard | ISO 15552 |
| Piston-rod end | Male thread |
| Design structure | Piston Piston rod Profile barrel |
| Position detection | For proximity sensor |
| Operating pressure MPa | 0.04 ... 1.2 MPa |
| Operating pressure | 0.4 ... 12 bar |
| Mode of operation | double-acting |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 3 - High corrosion stress |
| PWIS conformity | VDMA24364-B2-L |
| Cleanroom class | ISO class 6 |
| Ambient temperature | -20 ... 80 °C |
| Impact energy in end positions | 1 J |
| Cushioning length | 22 mm |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting | 990 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance | 1,178 N |
| Moving mass with 0 mm stroke | 363 g |
| Additional mass factor per 10 mm of stroke | 25 g |
| Basic weight for 0 mm stroke | 1,241 g |
| Additional weight per 10 mm stroke | 58 g |
| Mounting type | with internal (female) thread with accessories Optional |
| Pneumatic connection | G1/4 |
| Materials note | Conforms to RoHS |
| Material cover | Die-cast aluminium, coated |
| Material piston seal | TPE-U(PU) |
| Material piston | Wrought Aluminium alloy |
| Material piston rod | High alloy steel, non-corrosive |
| Material piston rod wiper seal | TPE-U(PU) |
| Buffer seal material | TPE-U(PU) |
| Cushion piston material | POM |
| Material cylinder barrel | Anodised wrought aluminium alloy |
| Material nut | High alloy steel, non-corrosive |
| Material bearing | POM |
| Material of flange screw | steel, galvanized |