

profile cylinder DNC-1 5/8"-5"-P

Part number: 177833

FESTO

per ISO 15552, with profile cylinder barrel, non-adjustable cushioning.



Data sheet

| Feature | Value |
|--|---|
| Stroke | 5 " |
| Piston diameter | 1 5/8" |
| Piston rod thread | 1/2-20 UNF-2A |
| Based on the standard | ISO 15552 (previously also VDMA 24652, ISO 6431, NF E49 003.1, UNI 10290) |
| Cushioning | P: Flexible cushioning rings/plates at both ends |
| Assembly position | Any |
| Piston-rod end | Male thread |
| Design structure | Piston Piston rod Profile barrel |
| Position detection | No |
| Variants | Single-ended piston rod |
| Operating pressure MPa | 0.06 ... 1.2 MPa |
| Operating pressure | 0.6 ... 12 bar |
| Mode of operation | double-acting |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -20 ... 80 °C |
| Impact energy in end positions | 0.2 J |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting | 633 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance | 754 N |
| Moving mass with 0 mm stroke | 307 g |
| Additional mass factor per 10 mm of stroke | 16 g |
| Basic weight for 0 mm stroke | 800 g |
| Additional weight per 10 mm stroke | 45 g |
| Mounting type | with internal (female) thread with accessories |
| Pneumatic connection | NPT1/4-18 |
| Materials note | Conforms to RoHS |
| Material cover | Aluminium die cast coated |
| Material seals | TPE-U(PU) |
| Material piston rod | High alloy steel |
| Material cylinder barrel | Wrought Aluminium alloy Smooth anodised |