



LFR-M1-G1/4-C07UGK

Filter regulator

| Feature | Data/description |
|--------------------------------|---|
| Size | 1 |
| Series | M |
| Actuator lock | Rotary knob with lock |
| Grade of filtration | 5 µm |
| Condensate drain | fully automatic |
| Design structure | Filter regulator with pressure gauge |
| Max. condensate volume | 10,25 cm ³ |
| Bowl guard | Plastic guard |
| Pressure gauge | with pressure gauge |
| Pressure control range | 0 - 7 bar |
| Inlet pressure 1 | 0 - 17 bar |
| Max. pressure hysteresis | 0,4 bar |
| Standard nominal flow rate | 1.900 l/min |
| Operating medium | Compressed air |
| Medium temperature | -10 - 80 °C |
| Ambient temperature | -10 - 80 °C |
| Product weight | 374 g |
| Mounting type | Optional Line installation with accessories |
| Pneumatic connection, port 1 | G1/4 |
| Pneumatic connection, port 2 | G1/4 |
| Materials note | Contains PWIS substances |
| Materials information, housing | Zinc die-casting |



Data sheet

Part no.: **179342**

Page:2

LFR-M1-G1/4-C07UGK**Filter regulator**

| Feature | Data/description |
|--------------------------------|------------------|
| Materials information for bowl | Zinc die-casting |