




LFM-M2-G1/4-XR

Micro filter

Feature	Data/description
Size	2
Series	M
Assembly position	Vertical +/- 5°
Filter efficiency	0,9999 %
Condensate drain	manual rotary
Design structure	Active carbon filter
Max. condensate volume	52,75 cm ³
Bowl guard	Plastic guard
Differential pressure display	Spirit level
Inlet pressure 1	0 - 12 bar
Flow characteristics (graph)	[Diagramm]
Standard nominal flow rate	680 l/min
Operating medium	Filtered, unlubricated compressed air, 0.01 µm filtration
Medium temperature	-10 - 30 °C
Residual oil content	0,003 mg/m ³
Ambient temperature	-10 - 30 °C
Mounting type	Optional Line installation with accessories
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 2	G1/4
Materials note	Contains PWIS substances
Materials information for filter	Active carbon
Materials information, housing	Zinc die-casting

**LFM-M2-G1/4-XR****Micro filter**

Feature	Data/description
Materials information for bowl	PA