


# Round cylinder ESAQ-4- -P

Part number: 183120

FESTO

End cap, with air connection perpendicular to cylinder axis  
This product is only available if ordered from Festo Korea Co. Ltd.



Exemplary representation

## Data sheet

Feature	Value
Stroke	1 ... 20 mm
Piston diameter	4 mm
Cushioning	P: Flexible cushioning rings/plates at both ends
Operating pressure	3 ... 10 bar
Mode of operation	single-acting pushing action
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2
Ambient temperature	-20 ... 80 °C
Theoretical force at 6 bar, advance stroke	4.7 N
Moving mass with 0 mm stroke	1.5 g
Additional weight per 10 mm stroke	0.8 g
Basic weight for 0 mm stroke	6 g
Additional mass factor per 10 mm of stroke	0.2 g
Pneumatic connection	M3
Materials information for cover	Wrought Aluminium alloy
Materials information for seals	NBR TPE-U(PU)
Materials information, housing	High alloy steel, non-corrosive
Materials information for piston rod	High alloy steel, non-corrosive