



## LFR-M2-G1/4-KF01

### Service unit combination

| Feature                      | Data/description  |
|------------------------------|---|
| Size                         | 2   |
| Series                       | M   |
| Actuator lock                | Rotary knob with lock   |
| Assembly position            | Vertical +/- 5°   |
| Grade of filtration          | 40 µm   |
| Condensate drain             | fully automatic   |
| Design structure             | Branching module<br>Pressure sensor<br>On/off valve<br>Filter regulator with pressure gauge |
| Max. condensate volume       | 52,75 cm <sup>3</sup>   |
| Bowl guard                   | Plastic guard   |
| Pressure gauge               | with pressure gauge   |
| Pressure control range       | 0 - 10 bar  |
| Inlet pressure 1             | 0 - 12 bar  |
| Max. pressure hysteresis     | 0,5 bar   |
| Standard nominal flow rate   | 1.800 l/min   |
| Operating medium             | Compressed air  |
| Medium temperature           | -10 - 60 °C   |
| Ambient temperature          | -10 - 60 °C   |
| Product weight               | 2.200 g   |
| Mounting type                | with accessories  |
| Pneumatic connection, port 1 | G1/4  |
| Pneumatic connection, port 2 | G1/4  |



## LFR-M2-G1/4-KF01

### Service unit combination

| Feature                        | Data/description                            |
|--------------------------------|---|
| Pneumatic connection, port 3   | G3/8  |
| Materials note                 | Contains PWIS substances                    |
| Materials information, housing | Zinc die-casting<br>Wrought Aluminium alloy |
| Materials information for bowl | PC  |