



## LFR-M2-G3/8-KB01

### Service unit combination

| Feature                      | Data/description   |
|------------------------------|--|
| Size                         | 2  |
| Series                       | M  |
| Actuator lock                | Rotary knob with lock  |
| Assembly position            | Vertical +/- 5°  |
| Grade of filtration          | 40 µm  |
| Condensate drain             | fully automatic  |
| Design structure             | Branching module<br>On/off valve<br>Filter regulator with pressure gauge |
| Max. condensate volume       | 52,75 cm <sup>3</sup>  |
| Bowl guard                   | Plastic guard  |
| Pressure gauge               | with pressure gauge  |
| Pressure control range       | 0 - 10 bar   |
| Inlet pressure 1             | 0 - 12 bar   |
| Max. pressure hysteresis     | 0,5 bar  |
| Standard nominal flow rate   | 3.800 l/min  |
| Operating medium             | Compressed air   |
| Medium temperature           | -10 - 60 °C  |
| Ambient temperature          | -10 - 60 °C  |
| Product weight               | 1.900 g  |
| Mounting type                | with accessories   |
| Pneumatic connection, port 1 | G3/8   |
| Pneumatic connection, port 2 | G3/8   |
| Pneumatic connection, port 3 | G3/8   |



Data sheet

Part no.: **184394**

Page:2

## LFR-M2-G3/8-KB01

### Service unit combination

| Feature                        | Data/description                            |
|--------------------------------|---|
| Pneumatic connection, port 4   | G1/4  |
| Materials note                 | Contains PWIS substances                    |
| Materials information, housing | Zinc die-casting<br>Wrought Aluminium alloy |
| Materials information for bowl | PC  |