


angle gripper HGWM-08-EO-G7

Part number: 185694

FESTO

Micro, with male thread.



Data sheet

Feature	Value
Size	8
Max. angular gripper jaw backlash ax,ay	0.5 deg
Max. gripper jaw backlash Sz	0.03 mm
Max. opening angle	17 deg
Repetition accuracy, gripper	≤ 0.02 mm
Number of gripper fingers	2
Drive system	pneumatic
Mode of operation	single-acting open
Gripper function	Angle
Gripper force back-up	No
Design structure	Inclined plane
Position detection	No
Operating pressure	2 ... 8 bar
Max. operating frequency of gripper	4 Hz
Min. opening time at 0.6 MPa (6 bar, 87 psi)	2.7 ms
Min. closing time at 0.6 MPa (6 bar, 87 psi)	1.2 ms
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B2-L
Ambient temperature	5 ... 60 °C
Spring return moment	0.5 Ncm
Total gripping torque at 0.6 MPa (6 bar, 87 psi) closing	22 Ncm
Max. force on gripper jaw Fz static	7 N
Max. torque at gripper Mx static	20 Ncm
Max. torque at gripper My static	20 Ncm
Max. torque at gripper Mz static	20 Ncm
Product weight	14 g
Mounting type	with lock nut
Pneumatic connection	M3
Materials note	Conforms to RoHS
Material cover cap	POM
Material housing	High alloy steel, non-corrosive
Material gripper jaws	High alloy steel