



MAS-20-N--AA-MOHK

Fluidic muscle

Feature	Data/description
Size	20
Hysteresis	< 4% of the length of the tubing
Max. contraction	25% of tubing length
Max. initial tension	3% of tubing length
Relaxation at room temperature	< 4% of the length of the tubing
Tubing length	60 - 9.000 mm
Repetition accuracy	< 1 %
Assembly position	Any
Operating pressure	0 - 6 bar
Mode of operation	single-acting pulling action
Operating medium	Lubricated compressed air Compressed air, filtered, unlubricated
Corrosion resistance classification CRC	2
Theoretical force at 6 bar	1.200 N
Additional weight per 1 m length	178 g
Product weight for 0 m length	253 g
Pneumatic connection	M16x1,5
Materials information for locknut	Wrought Aluminium alloy neutral anodisation
Materials note	Contains PWIS substances Copper and PTFE-free
Materials information for flange	Wrought Aluminium alloy blue anodised
Materials information for sleeve	Steel Galvanised



MAS-20-N--AA-MOHK

Fluidic muscle

Feature	Data/description
Materials information for membrane	CR AR