

# guided drive


## DFP-10-100-P-A-S2

Part number: 186768  
Product to be discontinued

FESTO

Protected against torsion, for proximity sensing, with double-ended piston rod.

Type to be discontinued. Available until 2018. See Support Portal for alternative products.



### Data sheet

Feature	Value
Stroke	100 mm
Piston diameter	10 mm
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Guide	Recirculating ball bearing guide
Design structure	Guide
Position detection	For proximity sensor
Variants	Through piston rod
Operating pressure	1.5 ... 10 bar
Max. speed	0.8 m/s
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	0 - No corrosion stress
Ambient temperature	-10 ... 60 °C
Impact energy in end positions	0.05 Nm
Theoretical force at 6 bar, return stroke	31 N
Theoretical force at 6 bar, advance stroke	31 N
Moving mass	59 g
Product weight	212 g
Pneumatic connection	M3
Materials note	Free of copper and PTFE
Material cover	Wrought Aluminium alloy
Material seals	NBR
Material housing	Wrought Aluminium alloy
Material piston rod	Heat-treatment steel