

suction cup ESS-200-SU

Part number: 189331

FESTO

easily interchangeable,



Data sheet

| Feature | Value |
|---|---|
| Min. workpiece radius | 680 mm |
| Nominal size | 10 mm |
| suction cup diameter | 200 mm |
| suction cup volume | 245.454 cm ³ |
| Position of connection | on top |
| Assembly position | Any |
| Correlation to suction-cup holder | Size 6 |
| Suction cup shape | round flat |
| Operating pressure MPa | -95 ... 0 kPa |
| Operating pressure | -0.95 ... 0 bar -13.775 ... 0 psi |
| Nominal operating pressure | -70 kPa -0.7 bar |
| Nominal operating pressure (psi) | -10.15 psi |
| Operating medium | Atmospheric air based on ISO 8573-1:2010 [7::-] |
| Corrosion resistance classification CRC | 1 - Low corrosion stress |
| PWIS conformity | VDMA24364 zone III |
| Food-safe | See Supplementary material information |
| Ambient temperature | -20 ... 60 °C |
| Retention force at nominal operating pressure | 1,610 N |
| Lateral force at nominal operating pressure | 1,000 N |
| Product weight | 1,198 g |
| Mounting type | Via vacuum port |
| Vacuum connection | M20x2 |
| Colour | blue |
| Shore hardness | 60 +/- 5 |
| Material of threaded plug | NBR Steel, nickel-plated Galvanised and chrome-plated steel |
| Materials note | Conforms to RoHS |
| Material suction cup | PUR |